

**TNMG 160408, Grade: CA125P****Order data**

Order number	251583 CA125P
GTIN	4960664024407
Item class	25E

Technical description

Grade	CA125P
Cutting speed v_c main application	150 - 320 m/min
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Cutting depth a_p	0.5 - 5 mm
Number of changes/inserts	6
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Chip breaker	PMG
Feed f	0.15 - 0.5 mm/rev.
Main application	P

Type of product

Indexable insert for turning