

**VNMG 160404, Grade: CA125P****Order data**

| | |
|--------------|---------------|
| Order number | 251752 CA125P |
| GTIN | 4960664014422 |
| Item class | 25E |

Technical description

| | |
|--------------------------------------|----------------------|
| ISO code indexable insert | VNMG 160408 |
| Corner radius | 0.8 mm |
| Cutting conditions | slightly interrupted |
| Main application | P |
| Grade | CA125P |
| Cutting depth a_p | 0.2 - 2.5 mm |
| Number of changes/inserts | 4 |
| Chip breaker | PQ |
| Finishing/roughing assignment | Finishing |
| Tool material | Carbide |
| Feed f | 0.13 - 0.4 mm/rev. |
| Cutting speed v_c main application | 150 - 320 m/min |

Type of product

Indexable insert for turning