


WN.G 080404, Grade: CA510


Order data

Order number	252112 CA510
GTIN	4960664700479
Item class	25E

Technical description

Chip breaker	PS
Cutting depth a_p	1 - 3.8 mm
Cutting speed v_c main application	80 - 450 m/min
Cutting conditions	continuous
Corner radius	0.4 mm
Main application	P
Feed f	0.15 - 0.6 mm/rev.
Grade	CA510
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6

Tolerance	M
Type of product	Indexable insert for turning