

**DC.T 11T304, Grade: CA125P****Order data**

Order number	260490 CA125P
GTIN	4960664018109
Item class	25E

Technical description

Main application	P
Cutting depth a_p	0.5 - 3 mm
Tolerance	M
Number of changes/inserts	2
Grade	CA125P
Chip breaker	GK
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	DCMT 11T304
Tool material	Carbide
Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing

Cutting speed v_c main application

90 - 260 m/min

Type of product

Indexable insert for turning