


DNMG 150608, Grade: CA115P

Order data

Order number	250697 CA115P
GTIN	4960664041879
Item class	25E

Technical description

Feed f	0.13 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 2.5 mm
Cutting speed v_c main application	180 - 400 m/min
Cutting conditions	continuous
Corner radius	0.8 mm
Grade	CA115P
Chip breaker	PQ
Main application	P
Number of changes/inserts	4
ISO code indexable insert	DNMG 150608
Tool material	Carbide

Type of product

Indexable insert for turning