

**DNMG 150608, Grade: CA115P****Order data**

Order number	250797 CA115P
GTIN	4960664046263
Item class	25E

Technical description

Main application	P
Cutting depth a_p	0.5 - 5 mm
Corner radius	0.8 mm
ISO code indexable insert	DNMG 150608
Cutting speed v_c main application	180 - 400 m/min
Chip breaker	PMG
Tool material	Carbide
Finishing/roughing assignment	Finishing
Feed f	0.15 - 0.6 mm/rev.
Number of changes/inserts	4
Cutting conditions	continuous
Grade	CA115P

Type of product

Indexable insert for turning