


WNMG 080412 wiper, Grade: CA510

Order data

Order number	252117 CA510
GTIN	4960664700417
Item class	25E

Technical description

Feed f	0.14 - 0.55 mm/rev.
Cutting depth a_p	0.5 - 3 mm
Chip breaker	WQ
Corner radius	1.2 mm
Main application	P
Cutting conditions	continuous
Cutting speed v_c main application	80 - 450 m/min
Grade	CA510
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080412
Number of changes/inserts	6

Type of product

Indexable insert for turning