


TNMG 160404, Grade: CA115P

Order data

Order number	251582 CA115P
GTIN	4960664046324
Item class	25E

Technical description

Corner radius	0.4 mm
Cutting conditions	continuous
Number of changes/inserts	6
Tool material	Carbide
Finishing/roughing assignment	Finishing
Grade	CA115P
Cutting depth a_p	0.5 - 5 mm
Chip breaker	PMG
ISO code indexable insert	TNMG 160404
Feed f	0.15 - 0.5 mm/rev.
Cutting speed v_c main application	180 - 400 m/min
Main application	P

Type of product

Indexable insert for turning