


WN.G 080404, Grade: KW10


Order data

Order number	252112 KW10
GTIN	4960664246588
Item class	25E

Technical description

Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Cutting depth a_p	1 - 4 mm
Cutting speed v_c main application	60 - 400 m/min
Feed f	0.1 - 0.35 mm/rev.
Chip breaker	AH
Main application	N
Grade	KW10
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6

Tolerance	M
Type of product	Indexable insert for turning