

**DC.T 11T302, Grade: CA115P****Order data**

Order number	260385 CA115P
GTIN	4960664045891
Item class	25E

Technical description

Cutting depth a_p	0.5 - 1.5 mm
Grade	CA115P
Feed f	0.05 - 0.25 mm/rev.
Cutting speed v_c main application	120 - 340 m/min
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting conditions	continuous
Number of changes/inserts	2
Tolerance	M
Chip breaker	HQ
ISO code indexable insert	DCMT 11T302

Main application	P
Type of product	Indexable insert for turning