



TNMG 160404, Grade: KW10

Order data

Order number	251582 KW10
GTIN	4960664220847
Item class	25E

Technical description

Chip breaker	AH
Cutting speed v_c main application	60 - 400 m/min
Main application	N
Cutting depth a_p	1 - 4 mm
Feed f	0.1 - 0.35 mm/rev.
Corner radius	0.4 mm
Cutting conditions	slightly interrupted
Grade	KW10
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning