



LED cordless floodlight, Power consumption: 39



Order data

Order number	081285 39
GTIN	5708997362051
Item class	08C

Description

Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

NOVA "For Life" cordless floodlight with integrated carrying handle and 5-step dimmer function.

- **New, updated design with highly efficient multi-LEDs.**
- **New OPTILight function for optimised light output and superior duration.**
- **Compact and durable for demanding work environments.**

Due to the dual system, can be used both as a mobile cordless floodlight, and also with mains cable.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery charger.

Technical description

Type of rechargeable battery	Lithium-ion
Overall height	275 mm
IP Index of Protection	IP 67
Illumination	600 - 6000 lm
Power supply	Mains operated
Power consumption	39 W
Overall length	275 mm
Overall width	92 mm