



LED floodlight, 230 V, Power consumption: 88W



Order data

Order number	081245 88
GTIN	5708997362068
Item class	08C

Description

Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

NOVA "For Life" LED floodlight with integrated carrying handle and 5-step dimmer function.

- **New, updated design with highly efficient multi-LEDs.**
- **New OPTILight function for optimised light output and superior duration.**
- **Compact and durable for demanding work environments.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Weight	4100 g
Overall height	298 mm
Overall width	102 mm
IP Index of Protection	IP 67

Connection cable length	5 m
Illumination	1200 - 12000 lm
Power supply	Mains-powered
Overall length	302 mm
Product name attribute	230 V
Type of product	Floodlight