

**Garant**
**Clamping toolholder, left-hand, Shank / insert size: 25/22mm**

**Order data**

Order number	251407 25/22
GTIN	4045197650948
Item class	21T

**Technical description**

Insert size	22 mm
Shim	259031 33
suitable indexable insert	TN.. 2204..
Pin	259049 2
Screw set	259023 2
Shank size	25 mm
ISO code toolholder	MTJNR/L 2525M22
Head length L <sub>1</sub>	36 mm
Functional width L <sub>4</sub>	32 mm
Clamping claw	259038 13
Overall length L	150 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 33	259031 33
Clamping claw Type 13	259038 13
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Set of screws 10 pieces Type 2	259023 2
Pin Type 2	259049 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500