



TNMG 160408 Set 10 pieces, Grade: HBX130



Order data

Order number	251603 HBX130
GTIN	4045197664914
Item class	22D

Description

TNMG 160408 Set of 10 pieces HBX130 Grade: HBX130

Chip breaker: MM

Cutting depth a_p : 1 - 6 mm

Feed f : 0.08 - 0.4 mm/rev.

Cutting speed v_c main application: 60 - 200 m/min

Technical description

Cutting depth a_p	1 - 6 mm
Cutting conditions	slightly interrupted
Chip breaker	MM
Main application	M
Corner radius	0.8 mm
Cutting speed v_c main application	60 - 200 m/min
Feed f	0.08 - 0.4 mm/rev.
Grade	HBX130

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TNMG 160408
Number of changes/inserts	6
Type of product	Indexable insert for turning