



## High-leverage flush cutter with 20° angled head, overall length: 200mm



### Order data

Order number	725610 200
GTIN	4003773081913
Item class	73F

### Description

#### Version:

Special compound action allows excellent cutting performance with relatively low applied force. Cutting edges induction hardened (approx. 59 HRC). Pliers chemically blacked, head bright polished, handles with multi-component covering. **With opening spring** and integral lock. **Head 20° offset for flush cutting.**

#### Application:

For flush cutting of soft materials such as plastic aluminium, copper (also Cu busbars up to 3×10 mm), lead.

#### Material:

Chrome-vanadium electric steel, forged and multi-stage oil-hardened.

### Technical description

overall length	200 mm
Cutting capacity soft wire up to Ø	6 mm
Blade	induction hardened
angled head	20 degrees
Handle	Multi-component covering
Material	Chrome vanadium electro-steel
Surface	chemically blacked
with return spring	yes

## Data sheet

with adjustment screw

yes

Type of product

Cutting pliers