



Cable cutter with 2-component grips VDE insulated, overall length: 225mm



Order data

Order number	730350 225
GTIN	4003773089964
Item class	73F

Description

Version:

Handles with **insulation up to 1000 volts to DIN EN IEC 60900 / VDE 0682-201**.

Handles with multi-component coverings. Head with sickle-shaped blades. Scissors gunmetal finish. Cuts smoothly and cleanly without crushing. **Two cutting areas:** The stepped main cutting edge keeps smaller and larger cables close to the scissors at all times so that they do not slip during cutting; the front cutting edge is used for step-by-step cutting ("nibbling") of very large cables. **Enormous capacity:** cuts single-stranded copper or aluminium cables up to 35 mm², multi-stranded cables up to 70 mm² and fine-stranded cables up to 120 mm².

Application:

For cutting copper and aluminium cables.

Material:

Special tool steel, drop-forged.

Technical description

Cutting capacity up to Ø	23 mm
Cutting capacity	120 mm ²
overall length	225 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Operation	mechanical, single-handed

Material	Special quality tool steel, drop-forged, oil-hardened
Surface	chrome-plated
with return spring	no
Type of product	Scissors