

Garant**Arbor for screw-in milling cutter, cylindrical, PSC 63, Thread size M: M16X50****Order data**

Order number	308553 M16X50
GTIN	4067263110118
Item class	31A

Description**Version:**

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

To take screw-in milling cutters with thread.

Technical description

Thread M	M16x50
Reach L ₁	50 mm
External Ø D	29 mm
Bore Ø D ₁	17 mm
Overhang dimension A	74.5 mm
Adapter	PSC 63
Arbor standard	ISO 26623-1
Through-coolant	yes
Concentricity	≤ 3 µm

Machining strategy	HPC
Type of product	Threaded copy mill arbor