



## Torque screwdriver set, 16 pieces fully insulated, maximum torque: 300cNm



### Order data

Order number	659356 300
GTIN	4013288229953
Item class	63F

### Description

#### Version:

Kraftform handle made of impact-resistant plastic with integral soft zones facilitates torque transmission and thus protects hand and arm. With colour coding for visual differentiation of the screw profiles. Handle and blade **fully insulated up to 1000 V to DIN EN 60900 / VDE 0682-201**.

#### Content:

Slot-head blades: 0.4×2.5; 0.6×3.5; 0.8×4.0; 1.0×5.5

Blades for Phillips: PH1 and PH2

Pozidriv bits: PZ1 and PZ2

blades for Torx®: Size TX10; TX15; TX20; TX25

Pozidriv-slot-head combination profile: PZ/ S1 and PZ/ S2 (combination profile)

Torque screwdriver: 1 pc.

Kraftform handle for interchangeable blades: 1 pc.

### Technical description

Drive profile	Screwdriver for TORX® screws
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver

Drive profile	Combination profile screwdriver Pozidriv/slot-head
Drive profile	Slot-head screwdriver
Measurement technology	mechanical
Direction of tightening	Right-hand tightening
maximum torque	300 cNm
Feedback	triggering
Reversible reading	cNm
Adjustable trigger value	adjustable
Setting the trigger value	with adjustment scale
Connection format	exchangeable blade
Release signalling	haptisk
Release signalling	acoustic
Data can be recorded	no
Torque range	1.2 - 3 Nm
Torque measuring accuracy	±6 %
Trigger principle	mechanical short-travel release
Torque range	120 - 300 cNm
Measurement process	Torque
Test certificate	Manufacturer's test certificate
Standard	DIN EN ISO 6789
Display	analogue
Manufacturer's designation	KK VDE 16 Torque 1.2-3.0 Nm
Type of product	Torque screwdriver

## Services

Calibration Torque screwdrivers, clockwise / anti-clockwise  
maximum torque 0,04-20/2 N·m

020260 0,04-20/2