

metabo**Construction site & workshop compressor, Type: 400/50D****Order data**

Order number	079842 400/50D
GTIN	4007430244468
Item class	03D

Description**Version:**

Powerful and robust compressor for demanding applications with instrument panel and belt drive.

Technical description

maximum suction rate	400 l/min
maximum pressure (air)	10 bar
Manufacturer's designation	400/50D
AC supply voltage	380-415 V
Power consumption	2.2 kW
Height	817 mm
Width	410 mm
Length	1050 mm
Pressure vessel volume	50 l
maximum filling rate	360 l/min

Weight	73 kg
Type of product	Compressor