



Pneumatic random orbital sander, Type: R036CC1HL



Order data

Order number	079657 R036CC1HL
GTIN	663023170923
Item class	03I

Description

Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level. Powerful random orbital sander for **external extraction system**. With a 5 mm orbital stroke.

Note:

See No. 567775 or 567901 for hook and loop grinding discs.

Technical description

Operating noise	82 dB(A)
maximum air consumption	498 l/min
Weight	0.9 kg
Backing pad Ø	150 mm
Stroke	5 mm
Type of extraction	External
maximum vibration to EN	3.9 m/s ²

maximum speed	13000 min ⁻¹
Power supply	Pneumatic
Type of product	Random orbital sander