

**Soldering station, Manufacturer's designation: NANOMK2****Order data**

Order number	082301 NANOMK2
GTIN	4003008153682
Item class	04K

Description**Version:**

Temperature-controlled soldering station with ceramic PTC heating element and internally-heated Ersadur long-life soldering tips (precise temperature control). Anti-static i-CON NANO microprocessor-controlled soldering station with high soldering heat output from an efficient high-power heating element. Solder tips are available with the ideal tip geometry for every soldering task.

Application:

For all professional electronics and electrical soldering applications.

Technical description

Power consumption	80 W
Control range of soldering tip temperature	150 - 450 °C
Height	103 mm
Power supply	Mains-powered
Warm-up time to 280 °C	9 s
Mains frequency	50 Hz
Length	145 mm
Weight of soldering iron without power cable	30 g

AC supply voltage	240 V
Width	80 mm
electrostatic characteristic	EGB/ESD
Type of product	Soldering station