




5-axis vice TeleCentric, Type: 125



Order data

Order number	361255 125
GTIN	
Item class	34A

Description

Version:

- **Optimum for use on 5-axis machining centres.**
- **Conventional clamping and gripper clamping can be performed.**
- **Telescopic spindles and obstructive contours remain unchanged.**
- **Simple centre-reference programming with no displacement of the zero point.**
- **Accessibility of the workpiece irrespective of the clamping span.**
- **Symmetrical design = workpiece remains central and parallel - the dimensions of the material are distributed symmetrically.**
- **Thanks to the quick-release fastening, pairs of jaws can be changed within 10 seconds.**
- **Constant clamping force thanks to the low-maintenance telescopic spindle.**
- **Supplied as standard with 25H6 M10 mounting holes for zero-point clamping system with 200 mm pitch.**
- **Integral scaled ring for fine adjustment of the centre position.**
- **Clamping force 30 kN at 45 Nm linear.**

Supplied with:

Hand crank, Quick Start Guide.

Optional extras:

Torque wrench No. 656050 size 120, hexagon screwdriver bit No. 643330 size 14, top jaws No. 361258 – 361264, clamp No. 360750 size 125/160, alignment and fixing set No. 360530, clamping stud No. 360025 size 25M10 or 25M10/138. Top jaws No. 361258 125 and 361260 125, additional optional accessories on request.

Technical description

Width B	125 mm
Series	TeleCentric
Clamping force up to maximum	40 kN
Width across flats	14 mm
maximum torque	60 Nm
Weight	35 kg
Length L	398 mm
Base body height c	178.9 mm
Clamping range S2	106 - 227 mm
Clamping range S1	44 - 165 mm
Height h	27.1 mm
Slot width n H7	20 mm
Version	Zero-point clamping system
Type of product	Machine vice

Accessories

ZeroClamp clamping stud with internal thread Type 25M10	360025 25M10
ZeroClamp clamping stud with internal thread Type 25M10/138	360025 25M10/138
Alignment and fixing set Table T-slot size 12 mm	360530 12
Alignment and fixing set Table T-slot size 14 mm	360530 14
Alignment and fixing set Table T-slot size 16 mm	360530 16
Alignment and fixing set Table T-slot size 18 mm	360530 18
Alignment and fixing set Table T-slot size 22 mm	360530 22
Clamp set2 pieces for jaw width 125/160 mm	360750 125/160
Top jawgripp Type 70	361258 70
Top jawsmooth Type 70	361260 70

Top jawprisma Type P	361264 P
Hexagon bit socket, long, 1/2 inch Hexagon 14 mm	643329 14
Torque wrenchwith reversible ratchet maximum torque 120 N·m	656050 120