

## Cordless wet / dry vacuum cleaner, Type: GAS1812MC



### Order data

Order number	070231 GAS1812MC
GTIN	4059952552682
Item class	03B

### Description

#### Version:

Cordless vacuum cleaner for mobile vacuuming. Easy transport and comfortable handling thanks to support loops on which the vacuum cleaner can be suspended. Rechargeable vacuum cleaner, dust protection class M.

- **Makes work easier thanks to Bosch's cable-free Auto-Start system.**
- **Superior suction power through brushless motor.**

#### Supplied with:

**Without battery and without charger.**

#### Note:

Suitable spare batteries and chargers can be found under No. 073851 – 073866. Refer to No. 070237 and onwards for the appropriate auto-start system.

### Technical description

Power supply	Mains operated
Length of suction hose	1.6 m
Manufacturer's designation	GAS 1812 MC
Battery voltage	18 V

Container volume	8 l
Type of rechargeable battery	Lithium-ion
Volumetric flow	1800 l/min
Weight without battery	8 kg
Number of rechargeable batteries contained	0
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Wet and dry vacuum cleaners

---

## Accessories

Battery charger Type GAL18V6-80	073866 GAL18V6-80
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Li-ion battery Battery type, battery voltage B18 V	073851 B18