



Chain lever hoist BRAVO™ with round steel link chain, Safe working load: 1,5t



Order data

Order number	086014 1,5
GTIN	3600232440598
Item class	08Y

Description

Version:

Hoist with **sheet steel casing**, extremely low weight, with **chain release as standard, low height, rotatable** bearing, forged hook.

Application:

Versatile hoist for use even under the most difficult conditions.

Note:

The principle of the **threaded load pressure brake** is that the axial braking force is generated by the load itself and is thus proportional to the weight of the load. The load is safely held in all positions; to lower it, the difference between the braking torque and load torque must be overcome. All Yale all-purpose hoists are equipped with this device.

The automatic **chain release** permits **quick run-out** of the unloaded chain; when the load is applied, the **threaded load pressure brake** automatically takes effect again and the load is safely held.

The **slip clutch** (optional feature) prevents unduly high loading, and thus increases the working life of the lifting gear.

Hoists with overload protection (slip clutch) available on request.

Technical description

Data sheet

Standard lifting height	1.5 m
Number of chains	1
Safe working load	1500 kg
Safe working load in t	1.5 t
minimum length between hooks	365 mm
Housing material	Steel
Chain release.	yes
Weight	11.5 kg
Lifting force at nominal load	400 daN
Chain link length	21 mm
Chain link Ø	7 mm
Type of product	Lever hoist / chain pull