

Garant
Clamping toolholder, neutral, Shank / insert size: 25/16mm

Order data

Order number	251712 25/16
GTIN	4045197649768
Item class	21T

Technical description

Overall length L neutral holders	150 mm
Overhang L ₁ neutral holders	45 mm
Functional width L ₄ neutral holders	12.5 mm
Shim screw	259025 3
Shank size	25 mm
suitable indexable insert	VN.. 1604..
Clamping claw	259038 2
ISO code toolholder	MVVNN 2525M16
Shim	259031 39
Insert size	16 mm
Screw for clamping claw	259021 1
Series	QuickTurn
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Screw for clamping claw Type 1	259021 1
Shim Type 39	259031 39
Shim screw Type 3	259025 3
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Clamping claw Type 2	259038 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500