

simatherm**Induction heating device, Size: 45****Order data**

Order number	883962 45
GTIN	2050002076488
Item class	86H

Description**Version:**

The compact simatherm® induction heating device for rolling bearings and other ring-shaped metal parts for bore diameters from 20 to 310 mm. Roller bearings and other ring-shaped metal parts can be brought up to the 110 °C specified by the manufacturer under automatic control of time and temperature. Particularly compact design – only 17 kg in weight including 3 yokes. Remote control possible via Bluetooth mobile devices (only with free app “World of Maintenance”)

Supplied with:

Heating device, 3 yokes, temperature probe and thermal protection gloves.

Technical description

Width	268 mm
Temperature control range	20 - 180 °C
Workpiece external Ø up to	310 mm
maximum component weight	45 kg
Voltage	230 V
Power	2.1 kW

Data sheet

Length	320 mm
Workpiece internal Ø from	20 mm
Height	293 mm
Type of product	Induction heater