

**Garant**
**DC.T 11T302, Grade: HU7310**


### Order data

Order number	260458 HU7310
GTIN	4045197669582
Item class	21G

### Description

DC.T 11T302 HU7310 Grade: HU7310  
 Chip breaker: AM  
 Tolerance: G  
 Cutting depth  $a_p$ : 0.1 - 4 mm  
 Feed  $f$ : 0.05 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 350 - 600 m/min

### Technical description

Chip breaker	AM
Cutting conditions	continuous
Cutting depth $a_p$	0.1 - 4 mm
Main application	N
Feed $f$	0.05 - 0.5 mm/rev.
Cutting speed $v_c$ main application	350 - 600 m/min

Corner radius	0.2 mm
Grade	HU7310
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	DCGT 11T302
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning