


**DCMT 070208, Grade: CA6525**

**Order data**

Order number	260486 CA6525
GTIN	4960664492008
Item class	25E

**Description**

DCMT 070208 CA6525 Grade: CA6525

Chip breaker: GK

Tolerance: M

Cutting depth  $a_p$ : 0.5 - 3 mm

Feed  $f$ : 0.1 - 0.3 mm/rev.

Cutting speed  $v_c$  main application: 50 - 140 m/min

**Technical description**

Cutting conditions	slightly interrupted
Chip breaker	GK
Corner radius	0.8 mm
Feed $f$	0.1 - 0.3 mm/rev.
Cutting speed $v_c$ main application	50 - 140 m/min
Main application	M
Cutting depth $a_p$	0.5 - 3 mm

Grade	CA6525
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DCMT 070208
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning