

**DC.T 11T304, Grade: KW10****Order data**

Order number	260490 KW10
GTIN	4960664359769
Item class	25E

Description

DC.T 11T304 KW10 Grade: KW10

Chip breaker: AH

Tolerance: G

Cutting depth a_p : 0.5 - 3 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 30 - 300 m/min

Technical description

Corner radius	0.4 mm
Cutting depth a_p	0.5 - 3 mm
Cutting speed v_c main application	30 - 300 m/min
Feed f	0.05 - 0.25 mm/rev.
Main application	N
Cutting conditions	continuous
Chip breaker	AH

Grade	KW10
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DCGT 11T304
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning