

**BDMT 070308 ER-JT, PR1810, Type: GG****Order data**

| | |
|--------------|---------------|
| Order number | 227160 GG |
| GTIN | 4960664026470 |
| Item class | 25A |

Description**Note:**

Standard application values for $a_e = 0.3 \times D$. Exactly 90° up to $a_p = 4$ mm.

Technical description

| | |
|---------------------------|------------------------------|
| Feed f_z per tooth | 0.09 – 0.16 mm |
| Corner radius | 0.8 mm |
| Grade | PR1810 |
| Type | GG |
| ISO code indexable insert | BDMT 070308 ER-JT |
| Grade | PR1810 |
| Tool material | Carbide |
| Type of product | Indexable insert for milling |

User data

| | Suitability | V_c | ISO code |
|-------------|---|----------------------|-----------------|
| GG(G) | suitable | 180 m/min | K |
| wet maximum | suitable only under restricted conditions | | |
| wet minimum | suitable only under restricted conditions | | |
| dry | suitable | | |
| Air | suitable | | |