



Indexable insert for milling BDMT 070308 ER-JT, for indexable milling cutters, PR1810



Order data

Order number	227160 GG
GTIN	4960664026470
Item class	25A

Description

Note:

Standard application values for $a_e = 0.3 \times D$. Exactly 90° up to $a_p = 4$ mm.

Technical description

Feed f_z per tooth	0.09 – 0.16 mm
Corner radius	0.8 mm
Type	PR1810
Type	GG
ISO code indexable insert	BDMT 070308 ER-JT
Type	PR1810
Tool material	Carbide
Coating	coated
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	180 m/min	K
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		