

**Garant**
**DC.T 070204, Grade: HU7310**


## Order data

Order number	260452 HU7310
GTIN	4045197669469
Item class	21G

## Description

### Technical description

Feed f	0.05 - 0.5 mm/rev.
Cutting speed $v_c$ main application	350 - 600 m/min
Cutting depth $a_p$	0.1 - 4 mm
Cutting conditions	continuous
Main application	N
Chip breaker	AM
Corner radius	0.4 mm
Grade	HU7310
Finishing/roughing assignment	Finishing
Tool material	Carbide

Coating	uncoated
ISO code indexable insert	DCGT 070204
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning