



Pneumatic small angle grinder, Type: RAM16L



Order data

Order number	079316 RAM16L
GTIN	5390145244526
Item class	03R

Description

Version:

Compact angle grinder with ergonomic design and narrow head for easy access in confined spaces. Durable and powerful angle grinder. 10° offset. With 6 mm collet chuck.

Technical description

maximum air consumption	1271 l/min
Connection thread	BSP
Weight	1.3 kg
Output power	370 W
Operating noise	73 dB(A)
recommended hose size (internal Ø)	8 mm
Compressed air connection	1/4 in
maximum speed	16000 min ⁻¹
maximum vibration to EN	4.41 m/s ²
maximum disc Ø	75 mm

Type of product

Angle grinder