



Cordless drill/driver, Type: 71161461H1



Order data

Order number	070205 71161461H1
GTIN	
Item class	03F

Description

Version:

2 and 4 speed cordless drill/driver

- For precise drilling and screwdriving results.
- Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.
- Sturdy metal gearbox for long working life.
- Good weight balance and ergonomics with softgrip inserts for non-tiring continuous work.
- Maximum work progress with AMPShare 18V ProCore rechargeable batteries: COOLPACK 2.0 technology provides 135% longer battery life. State-of-the-art cell technology and intelligent battery management provide 87% more power than conventional batteries.

Small and light 4-speed cordless drill/driver with brushless motor and QuickIN interface. Perfectly suited to universal drilling and screwdriving work up to 8 mm.

- Solid metal 4-speed gearbox for optimum cutting speeds for drilling in metal and self-tapping screwdriving work up to 6 mm.
- Brushless FEIN PowerDrive motor with 30% higher efficiency and long working life.
- Mechanical torque setting.
- Extensive user protection features include restart protection, electronic overload protection and brake.

Supplied with:

Supplied with battery and charger.

Technical description

Weight	1.8 kg
Battery capacity	4 Ah
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum twist drill size Ø in steel	13 mm
maximum speed 3rd speed	1400 min ⁻¹
maximum speed 2nd speed	700 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
maximum speed 4th speed	2500 min ⁻¹
maximum twist drill size Ø in wood	40 mm
maximum vibration to EN	<2,5 m/s ²
maximum speed 1st speed	400 min ⁻¹
Power supply	Mains operated
typical application	Medium
Manufacturer's designation	ASCM 18 QSW AS
maximum torque hard	40 Nm
Packaging	Modular case (L-Boxx)
maximum torque soft	30 Nm
Type of product	Drill/driver
USP1	18V, 2-speed
USP2	Quick-release chuck clamping range 1.5-13, in a carrying case

