


Garant**Manual vice for drilling machines, with eccentric quick clamping, Jaw width A: 100mm****Order data**

Order number	365038 100
GTIN	4067263112389
Item class	31S

Description**Version:**

- **Sturdy design with strong spindle.**
- **Jaws through hardened and ground.**
- **Precise clamping due to long flat guide.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**

Patent-pending **integrated eccentric quick clamping** for a secure grip on the drilling machine table.

Application:

For clamping components on drilling machines.

Material:

Body and movable jaw made of special cast iron.

Accuracy:

Within **0.10 mm.**

Supplied with:

Clamp wrenches and three Tee-nuts in sizes 12;14 and 16 mm.

Technical description

Overall height c	92 mm
------------------	-------

Base body length a	286 mm
Colour code for suitable accessories	BM vice, blue
Jaw width A	100 mm
Base body width B	174 mm
Jaw height C	32 mm
Clamping range b	143 mm
Clamping slot width	17 mm
Clamping slot spacing	141 mm
maximum overall length L ₄	474 mm
Weight	12.5 kg
Type of product	Drilling machine vice

Accessories

Slide for No. 365023	365025
Backstop Type 1	365028 1
Pair of spare jaws (2 pieces) for quick-release vice or drilling machine vice for type 100	365036 100
Spare spindle for manual vice for drilling machines for type 100	365037 100
Eccentric clamping unit Type 1	365039 1