


Garant**Manual vice for drilling machines, with eccentric quick clamping, Jaw width A: 120mm****Order data**

Order number	365038 120
GTIN	4067263112396
Item class	31S

Description**Version:**

- **Sturdy design with strong spindle.**
- **Jaws through hardened and ground.**
- **Precise clamping due to long flat guide.**
- **One jaw with horizontal and vertical prismatic profiles for round material, one jaw smooth.**
- **Both jaws are stepped at the top to clamp flat parts.**

Patent-pending **integrated eccentric quick clamping** for a secure grip on the drilling machine table.

Application:

For clamping components on drilling machines.

Material:

Body and movable jaw made of special cast iron.

Accuracy:

Within **0.10 mm**.

Supplied with:

Clamp wrenches and three Tee-nuts in sizes 12;14 and 16 mm.

Technical description

Clamping slot spacing	160 mm
-----------------------	--------

Jaw width A	120 mm
Weight	20 kg
Clamping range b	173 mm
Base body length a	340 mm
Colour code for suitable accessories	BM vice, grey
Base body width B	193 mm
Overall height c	107 mm
Jaw height C	40 mm
Clamping slot width	17 mm
maximum overall length L ₄	556 mm
Type of product	Drilling machine vice

Accessories

Slide for No. 365023	365025
Backstop Type 2	365028 2
Pair of spare jaws (2 pieces) for quick-release vice or drilling machine vice for type 120	365036 120
Spare spindle for manual vice for drilling machines for type 120	365037 120
Eccentric clamping unit Type 1	365039 1