


**CNMG 160612, Grade: CA125P****Order data**

Order number	250377 CA125P
GTIN	4960664013920
Item class	25E

Technical description

Cutting speed v_c main application	140 - 300 m/min
Feed f	0.28 - 0.88 mm/rev.
Chip breaker	PH
Cutting depth a_p	1 - 10 mm
Main application	P
Cutting conditions	slightly interrupted
Grade	CA125P
ISO code indexable insert	CNMG 160612
Number of changes/inserts	4
Finishing/roughing assignment	Roughing
Tool material	Carbide
Corner radius	1.2 mm

Type of product

Indexable insert for turning