



CNMM 190612, Grade: CA125P

Order data

Order number	250503 CA125P
GTIN	4960664014835
Item class	25E

Technical description

Tool material	Carbide
Grade	CA125P
Cutting depth a_p	1 - 11 mm
Cutting conditions	slightly interrupted
Chip breaker	PX
Main application	P
Corner radius	1.2 mm
ISO code indexable insert	CNMM 190612
Finishing/roughing assignment	Roughing
Number of changes/inserts	4
Feed f	0.25 - 0.9 mm/rev.
Cutting speed v_c main application	140 - 300 m/min

Type of product

Indexable insert for turning