

**WNMG 080408, Grade: CA125P****Order data**

Order number	252014 CA125P
GTIN	4960664017270
Item class	25E

**Technical description**

Cutting depth $a_p$	0.5 - 2 mm
Feed $f$	0.07 - 0.3 mm/rev.
Chip breaker	HQ
Cutting conditions	slightly interrupted
Grade	CA125P
Number of changes/inserts	6
ISO code indexable insert	WNMG 080408
Cutting speed $v_c$ main application	150 - 320 m/min
Corner radius	0.8 mm
Main application	P
Tool material	Carbide
Finishing/roughing assignment	Finishing

Type of product

Indexable insert for turning