

**DNMG 150604, Grade: CA125P****Order data**

Order number	250796 CA125P
GTIN	4960664024322
Item class	25E

Technical description

Tool material	Carbide
Number of changes/inserts	4
Grade	CA125P
Corner radius	0.4 mm
Feed f	0.15 - 0.6 mm/rev.
Cutting speed v_c main application	150 - 320 m/min
Main application	P
Finishing/roughing assignment	Finishing
Chip breaker	PMG
ISO code indexable insert	DNMG 150604
Cutting depth a_p	0.5 - 5 mm
Cutting conditions	slightly interrupted

Type of product

Indexable insert for turning