


DNMG 150608, Grade: CA125P

Order data

Order number	250892 CA125P
GTIN	4960664015290
Item class	25E

Technical description

ISO code indexable insert	DNMG 150608
Cutting conditions	slightly interrupted
Grade	CA125P
Main application	P
Cutting speed v_c main application	140 - 300 m/min
Cutting depth a_p	1 - 5 mm
Number of changes/inserts	4
Tool material	Carbide
Corner radius	0.8 mm
Chip breaker	PH
Feed f	0.25 - 0.6 mm/rev.
Finishing/roughing assignment	Roughing

Type of product

Indexable insert for turning