

**VBMT 160408, Grade: CA125P****Order data**

Order number	261184 CA125P
GTIN	4960664016693
Item class	25E

Technical description

Main application	P
Chip breaker	HQ
Cutting speed v_c main application	110 - 260 m/min
Cutting depth a_p	0.5 - 2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Corner radius	0.8 mm
Grade	CA125P
Cutting conditions	slightly interrupted
Number of changes/inserts	2
Feed f	0.05 - 0.25 mm/rev.
ISO code indexable insert	VBMT 160408

Type of product

Indexable insert for turning