

Garant

GARANT Master Steel solid carbide high-performance drill DIN 6535 HA, TiAlN, Ø DC h7: 6,6mm



Order data

| | |
|--------------|---------------|
| Order number | 122761 6,6 |
| GTIN | 4067263121527 |
| Item class | 11E |

Description

Version:

Robust drill design and optimised special point geometry for the **best possible chip formation and reliable chip breakage** with **higher feed rates at the same time**. **Advanced micro-geometry, convex cutting edge and conical profile grinding** to provide additional stability for the main cutting edge. **Optimised flute geometry and patented face geometry** for **reliable chip evacuation** in steel materials and cast material. **High-performance coating** of the latest generation.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.

HB shanks: order with **No. 122762**.

HE shank: order with **No. 122761 + 129100HE**.

Technical description

| | |
|---------------------------------------------------|----------|
| Standard | DIN 6537 |
| Shank Ø D _s | 8 mm |
| Overall length L | 91 mm |
| Number of cutting edges Z | 2 |
| Tolerance nominal Ø | h7 |
| recommended maximum drilling depth L ₂ | 43.1 mm |
| Nominal Ø D _c | 6.6 mm |

| | |
|-------------------------------------------|-------------------|
| Flute length L_c | 53 mm |
| Feed f in steel $< 1100 \text{ N/mm}^2$ | 0.22 mm/rev. |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 6xD |
| Point angle | 140 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|-------------------------------------------|-----------|----------|
| Steel $< 500 \text{ N/mm}^2$ | suitable | 170 m/min | P |
| Steel $< 750 \text{ N/mm}^2$ | suitable | 155 m/min | P |
| Steel $< 900 \text{ N/mm}^2$ | suitable | 145 m/min | P |
| Steel $< 1100 \text{ N/mm}^2$ | suitable | 130 m/min | P |
| Steel $< 1400 \text{ N/mm}^2$ | suitable | 110 m/min | P |
| Steel $< 55 \text{ HRC}$ | suitable | 60 m/min | H |
| INOX $< 900 \text{ N/mm}^2$ | suitable only under restricted conditions | 55 m/min | M |
| INOX $> 900 \text{ N/mm}^2$ | suitable only under restricted conditions | 45 m/min | M |
| GG | suitable | 130 m/min | K |
| GGG | suitable | 90 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |

| | |
|-------------|----------|
| wet minimum | suitable |
| Air | suitable |