

**TNMG 160404, Grade: CA125P****Order data**

Order number	251472 CA125P
GTIN	4960664014323
Item class	25E

Technical description

Number of changes/inserts	6
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 2.5 mm
Corner radius	0.4 mm
ISO code indexable insert	TNMG 160404
Feed f	0.13 - 0.4 mm/rev.
Grade	CA125P
Tool material	Carbide
Main application	P
Cutting speed v_c main application	150 - 320 m/min
Chip breaker	PQ

Type of product

Indexable insert for turning