


DNMG 150616, Grade: CA125P

Order data

Order number	250894 CA125P
GTIN	4960664015313
Item class	25E

Technical description

Corner radius	1.6 mm
Number of changes/inserts	4
Chip breaker	PH
Feed f	0.25 - 0.6 mm/rev.
ISO code indexable insert	DNMG 150616
Finishing/roughing assignment	Roughing
Grade	CA125P
Main application	P
Cutting conditions	slightly interrupted
Cutting speed v_c main application	140 - 300 m/min
Cutting depth a_p	1 - 5 mm
Tool material	Carbide

Type of product

Indexable insert for turning