

**VBMT 160404, Grade: CA125P****Order data**

Order number	261182 CA125P
GTIN	4960664016686
Item class	25E

Technical description

Feed f	0.05 - 0.25 mm/rev.
Tool material	Carbide
Cutting conditions	slightly interrupted
Main application	P
Number of changes/inserts	2
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Grade	CA125P
Chip breaker	HQ
ISO code indexable insert	VBMT 160404
Cutting speed v_c main application	110 - 260 m/min
Cutting depth a_p	0.5 - 2 mm

Type of product

Indexable insert for turning