

**TNMG 160404, Grade: CA125P****Order data**

Order number	251582 CA125P
GTIN	4960664024391
Item class	25E

Technical description

Number of changes/inserts	6
Tool material	Carbide
Grade	CA125P
Main application	P
Chip breaker	PMG
Corner radius	0.4 mm
Cutting depth a_p	0.5 - 5 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 320 m/min
Cutting conditions	slightly interrupted
ISO code indexable insert	TNMG 160404
Feed f	0.15 - 0.5 mm/rev.

Type of product

Indexable insert for turning