


**SNMG 190612, Grade: CA125P****Order data**

Order number	251368 CA125P
GTIN	4960664015658
Item class	25E

Technical description

Cutting speed v_c main application	140 - 330 m/min
Tool material	Carbide
Cutting depth a_p	1 - 11 mm
ISO code indexable insert	SNMG 190612
Main application	P
Chip breaker	PH
Feed f	0.3 - 1 mm/rev.
Number of changes/inserts	8
Finishing/roughing assignment	Roughing
Grade	CA125P
Corner radius	1.2 mm
Cutting conditions	slightly interrupted

Type of product

Indexable insert for turning