


**SNMG 120408, Grade: CA125P****Order data**

Order number	251254 CA125P
GTIN	4960664024360
Item class	25E

**Technical description**

ISO code indexable insert	SNMG 120408
Cutting depth $a_p$	0.5 - 5 mm
Grade	CA125P
Corner radius	0.8 mm
Cutting conditions	slightly interrupted
Main application	P
Chip breaker	PMG
Number of changes/inserts	8
Cutting speed $v_c$ main application	150 - 320 m/min
Tool material	Carbide
Finishing/roughing assignment	Finishing
Feed $f$	0.15 - 0.5 mm/rev.

Type of product

Indexable insert for turning